

**DIRECTLY-HEATED
FULL-WAVE RECTIFIER**



D.W.2

OPERATING DATA.

Filament Voltage	4·0 V.
Filament Current	1·0 A.
Max. Anode Voltage			250-0-250 V. r.m.s.

OUTPUT.

Maximum rectified current
60 mA D.C. at 250 V.

PRICE 10/6

**DIRECTLY-HEATED
FULL-WAVE RECTIFIER**

D.W.4/350

OPERATING DATA.

Filament Voltage	4·0 V.
Filament Current	2·0 A.
Max. Anode Voltage			350-0-350 V. r.m.s.

OUTPUT.

Maximum rectified current
120 mA D.C. at 350 V.

PRICE 10/6

**DIRECTLY-HEATED
FULL-WAVE RECTIFIER**

D.W.4/500

OPERATING DATA.

Filament Voltage	4·0 V.
Filament Current	2·0 A.
Max. Anode Voltage			500-0-500 V. r.m.s.

OUTPUT.

Maximum rectified current
120 mA D.C. at 500 V.

PRICE 15/-