

MULLARD RECEIVING VALVES

for use with

6-VOLT L.T. ACCUMULATOR

| Type. | Application. | For particulars see page | PRICE | |
|---------|---|--------------------------|----------------|-----------|
| | | | In Gt. Britain | In I.F.S. |
| PM.16 | Screened-grid high frequency amplifier .. | 25 | 20/- | 22/- |
| PM.5B | High frequency amplifier or detector followed by resistance-capacity coupling .. | 26 | 8/6 | 9/6 |
| PM.5D | Detector or low frequency amplifier followed by transformer or resistance-capacity coupling | 27 | 8/6 | 9/6 |
| PM.5X | Detector or low frequency amplifier followed by transformer coupling | 28 | 8/6 | 9/6 |
| PM.6D | Super detector or low frequency amplifier followed by transformer coupling .. | 29 | 8/6 | 9/6 |
| PM.6 | Small power valve .. | 30 | 10/6 | 11/9 |
| PM.256 | Super power valve .. | 31 | 13/6 | 15/- |
| PM.256A | Super power valve .. | 32 | 13/6 | 15/- |
| PM.26 | Pentode output valve | 33 | 20/- | 22/- |

Mullard the Master Valve